

The SleepSafer® provides protection up to 36¼" above the mattress

SleepSafer® Tall Bed



SleepSafer® (Tall Bed) Measurements and Specifications:

SAFETY RAIL HEIGHT(S) OF FOUNDATION

(Distance from the top of rail to the top of mattress)

Fixed Foundation with Box Spring	31" or 24¾"
Fixed Foundation with Bunkie Board	36¼" or 30"
Manual Articulation	34" or 27¾"
Manual HI-LO	LO 30½" to HI 18¾"
Manual HI-LO Combo	LO 30½" to HI 18¾"
Manual Electric Combo	LO 30½" to HI 18¾"
Electric Articulation	34" or 27¾"
Electric HI-LO Combo	LO 30½" to HI 20¾"

OVERALL OUTSIDE DIMENSIONS

Twin	42¼" W x 80¼" L x 56" H
Full	56" W x 80" L x 57" H
Queen	65" W x 80" L x 57" H

MATTRESS SIZE (Without pads / With pads / Length)

Twin	38" W / 36" W / 77" L
Full	52" W / 50" W / 77" L
Queen	61" W / 60" W / 77" L

MATTRESS TO FLOOR HEIGHT(S) OF FOUNDATION

(Distance from the floor to the top of mattress)

Fixed Foundation with Box Spring	23¾" or 30"
Fixed Foundation with Bunkie Board	18½"
Manual Articulating	20¾" or 27"
Manual HI-LO	LO 24¼" to HI 36"
Manual HI-LO Combo	LO 24¼" to HI 36"
Manual Electric Combo	LO 24¼" to HI 36"
Electric Articulation	20¾" or 27"
Electric HI-LO Combo	LO 24¼" to HI 34½"

FLOOR TO RAIL HEIGHT 54¾"

UNDER BED FLOOR CLEARANCE 7¾"

TRANSFER HEIGHT

With rails attached / detached 26" / 24½"

AVAILABLE OPTIONS

Padding over or around windows (8 colors available);
Solid clear or mesh windows; IV pole; Tubing Channel Access
Cut Out; Headboard and/or footboard windows.