


Safety Rail Heights – 3 Models

LOW – This is our classic *SleepSafe*® bed with safety rails ranging up to 17¼” above the mattress depending on the foundation choice.

MEDIUM – The *SleepSafe*® II provides protection ranging up to 27” above the mattress depending on the foundation choice.

TALL – The *SleepSafer*® provides protection up to 36¼” above the mattress depending on the foundation choice. The *SleepSafer*® Extension Kit offers an **additional 16¾” of safety rail height** when ordered or retrofitted to your existing *SleepSafer*® Bed.



<i>SleepSafe</i> ® Bed Specifications	Low Bed <i>SleepSafe</i> ®	Medium Bed <i>SleepSafe</i> ® II	Tall Bed / Extension <i>SleepSafer</i> ®
SAFETY RAIL HEIGHT <i>The distance from the top of mattress to the top of the safety rail.</i>			
Fixed Foundation with Box Spring (<i>Choice of settings</i>)	12” or 8¾”	17¾”, 14” or 10”	31” or 24¾” / 47¾” or 41½”
Fixed Foundation with Bunkie Board (<i>Choice of settings</i>)	17¼” or 14”	27” or 21¾”	36¼” / 53”
Manual Articulation	15” or 11¾”	21”, 17” or 13¼”	34” or 27¾” / 50¾” or 44½”
Manual HI-LO , HI-LO Combo and Electric	LO 11½” to EVEN with rail	LO 21¼” to HI 9½” or LO 16” to HI 4¼”	LO 30½” to HI 18¾” / LO 47½” to HI 35¾”
Electric Articulation (<i>Choice of settings</i>)	15” or 11¾”	21”, 17” or 13¼”	34” or 27¾” / 50¾” or 44½”
Electric HI-LO Foundation (<i>LO to HI Settings</i>)	LO 11½” to HI 1¼” below rail	LO 21¼” to HI 11” or LO 16” to HI 5¾”	LO 30½” to HI 20¾” / LO 47½” to HI 37¼”
MATTRESS HEIGHT <i>The distance from the top of the mattress to the floor.</i>			
Fixed Foundation with Box Spring (<i>Choice of settings</i>)	23¾” or 27”	28”, 32” or 35½”	23¾” or 30”
Fixed Foundation with Bunkie Board (<i>Choice of settings</i>)	18½” or 21¾”	18¾” or 24”	18½”
Manual Articulation	20¾” or 24”	25”, 28¾” or 32½”	20¾” or 27”
Manual HI-LO , HI-LO Combo and Electric	LO 24¼” to HI 36”	LO 24½” to HI 36¼” or LO 29¾” to HI 41½”	LO 24¼” to HI 36”
Electric Articulation (<i>Choice of settings</i>)	20¾” or 24”	25”, 28¾” or 32½”	20¾” or 27”
Electric HI-LO - (<i>LO to HI Settings</i>)	LO 24¼” to HI 34½”	LO 24½” to HI 34¾” or LO 29¾” to HI 40”	LO 24¼” to HI 34½”
FLOOR TO RAIL HEIGHT <i>The distance from the top of the rail to the floor.</i>	35¾”	45¾”	54¾” / 72”
OVERALL OUTSIDE DIMENSIONS			
Twin	42¼”W x 80½”L x 40¾”H	42¼”W x 80½”L x 50¾”H	42¼”W x 80¼”L x 56”H (72¾”H w/Ext.)
Full	56”W x 80”L x 40¾”H	56”W x 80”L x 50¾”H	56”W x 80”L x 57”H (72¾”H w/Ext.)
Queen	65”W x 80”L x 40¾”H	65”W x 80”L x 50¾”H	65”W x 80”L x 57”H (72¾”H w/Ext.)
MATTRESS SIZE <i>Width without pads / Width with pads / Length</i>			
Twin	38”W / 36”W / 77”L	38”W / 36”W / 77”L	38”W / 36”W / 77”L
Full	51”W / 50”W / 77”L	51”W / 50”W / 77”L	51”W / 50”W / 77”L
Queen	61”W / 60”W / 77”L	61”W / 60”W / 77”L	61”W / 60”W / 77”L
UNDER BED FLOOR CLEARANCE			
Standard Models	8”	8”	7¾”
TRANSFER HEIGHT <i>The distance from top edge of the folded down safety rail to the floor.</i>	22¼” with Safety Rail On 20¾” with Safety Rail Off	32” with Safety Rail On 30½” with Safety Rail Off	26” with Safety Rail On 24½” with Safety Rail Off

