



SleepSafe® Bed Model Measurements

Use this chart to compare the different measurement specifications from model to model.

SleepSafe Bed, LLC
3629 Reed Creek Dr.
Bassett, VA 24055

Toll Free: 866.852.2337
SleepSafeBed.com

SleepSafe® Bed Specifications	Low Bed SleepSafe®	Medium Bed SleepSafe® II	Tall Bed / Extension Bed SleepSafer®
FOUNDATION SAFETY RAIL HEIGHTS <i>The distance from the top of mattress to the top of the safety rail.</i>			
Fixed w/Box Spring (Frame attachment choice)	12" or 8¾"	17¾", 14" or 10"	31" or 24¾" / 47¾" or 41½"
Fixed w/Bunkie Board (Frame attachment choice)	17¼" or 14"	27" or 21¾"	36¼" or 30" / 53" or 46¾"
Manual Articulation (Frame attachment choice)	15" or 11¾"	21", 17" or 13¼"	34" or 27¾" / 50¾" or 44½"
Manual Electric Combo (LO to HI Settings based on frame attachment)	LO 11½" to EVEN with rail	LO 21¼" to HI 9½" or LO 16" to HI 4¼"	LO 30½" to HI 18¾" / LO 47½" to HI 35¾"
Manual Hi-Lo (LO to HI Settings based on frame attachment)	LO 11½" to EVEN with rail	LO 21¼" to HI 9½" or LO 16" to HI 4¼"	LO 30½" to HI 18¾" / LO 47½" to HI 35¾"
Manual Hi-Lo Combo (LO to HI Settings based on frame attachment)	LO 11½" to EVEN with rail	LO 21¼" to HI 9½" or LO 16" to HI 4¼"	LO 30½" to HI 18¾" / LO 47½" to HI 35¾"
Electric Articulation (Frame attachment choice)	15" or 11¾"	21", 17" or 13¼"	34" or 27¾" / 50¾" or 44½"
Electric Hi-Lo Combo (LO to HI Settings based on frame attachment)	LO 11½" to HI 1¼" below rail	LO 21¼" to HI 11" or LO 16" to HI 5¾"	LO 30½" to HI 20¾" / LO 47½" to HI 37¼"
FOUNDATION MATTRESS TO FLOOR HEIGHTS <i>The distance from the top of the mattress to the floor.</i>			
Fixed w/Box Spring (Frame attachment choice)	23¾" or 27"	28", 32" or 35½"	23¾" or 30"
Fixed w/Bunkie Board (Frame attachment choice)	18½" or 21¾"	18¾" or 24"	18½" or 24¾"
Manual Articulation (Frame attachment choice)	20¾" or 24"	25", 28¾" or 32½"	20¾" or 27"
Manual Electric Combo (LO to HI Settings based on frame attachment)	LO 24¼" to HI 36"	LO 24½" to HI 36¼" or LO 29¾" to HI 41½"	LO 24¼" to HI 36"
Manual Hi-Lo (LO to HI Settings based on frame attachment)	LO 24¼" to HI 36"	LO 24½" to HI 36¼" or LO 29¾" to HI 41½"	LO 24¼" to HI 36"
Manual Hi-Lo Combo (LO to HI Settings based on frame attachment)	LO 24¼" to HI 36"	LO 24½" to HI 36¼" or LO 29¾" to HI 41½"	LO 24¼" to HI 36"
Electric Articulation (Frame attachment choice)	20¾" or 24"	25", 28¾" or 32½"	20¾" or 27"
Electric Hi-Lo Combo (LO to HI Settings based on frame attachment)	LO 24¼" to HI 34½"	LO 24½" to HI 34¾" or LO 29¾" to HI 40"	LO 24¼" to HI 34½"
FLOOR TO RAIL HEIGHT <i>The distance from the floor to the top of the rail.</i>	35¾"	45¾"	54¾" / 72"
OVERALL OUTSIDE DIMENSIONS			
Twin	42¼" W x 80½" L x 40¾" H	42¼" W x 80½" L x 50¾" H	42¼" W x 80¼" L x 57" H (72¾" H w/Ext.)
Full	56" W x 80" L x 40¾" H	56" W x 80" L x 50¾" H	56" W x 80" L x 57" H (72¾" H w/Ext.)
Queen	65" W x 80" L x 40¾" H	65" W x 80" L x 50¾" H	65" W x 80" L x 57" H (72¾" H w/Ext.)
MATTRESS SIZE <i>Width without pads / Width with pads / Length</i>			
Twin / Full / Queen	38" W / 36" W / 77" L	52" W / 50" W / 77" L	61" W / 60" W / 77" L
UNDER BED FLOOR CLEARANCE			
Standard Models	8"	8"	7¾"
TRANSFER HEIGHT <i>The distance from top edge of the folded down safety rail to the floor.</i>	22¼" with Safety Rail On 20¾" with Safety Rail Off	32" with Safety Rail On 30½" with Safety Rail Off	26" with Safety Rail On 24½" with Safety Rail Off



Photo Reference Guide for Bed Measurements

