

SleepSafe® Bed Model Measurements

Use this chart to compare the different measurement specifications from model to model.

SleepSafe Bed, LLC 3629 Reed Creek Dr. Bassett, VA 24055


Toll Free: 866.852.2337 SleepSafeBed.com

SleepSafe® Bed	Low Bed	Medium Bed	Tall Bed / Extension Bed
Specifications	SleepSafe®	SleepSafe® II	SleepSafer®
FOUNDATION SAFETY RAIL HEIGHTS The distance from	the top of mattress to the top o	f the safety rail.	
Fixed w/Box Spring (Frame attachment choice)	12" or 8¾"	17¾", 14" or 10"	31" or 24¾" / 47¾" or 41½"
Fixed w/Bunkie Board (Frame attachment choice)	17¼" or 14"	27" or 21¾"	36¼" or 30" / 53" or 46¾"
Manual Articulation (Frame attachment choice)	15" or 11¾"	21", 17" or 131/4"	34" or 27¾" / 50¾" or 44½"
Manual Electric Combo (LO to HI Settings based on frame attachment)	LO 11½" to EVEN with rail	LO 21¼" to HI 9½" or LO 16" to HI 4¼"	LO 30½" to HI 18¾" / LO 47½" to HI 35¾"
Manual Hi-Lo (LO to HI Settings based on frame attachment)	LO 11½" to EVEN with rail	LO 21¼" to HI 9½" or LO 16" to HI 4¼"	LO 30½" to HI 18¾" / LO 47½" to HI 35¾"
Manual Hi-Lo Combo (LO to HI Settings based on frame attachment)	LO 11½" to EVEN with rail	LO 21¼" to HI 9½" or LO 16" to HI 4¼"	LO 30½" to HI 18¾" / LO 47½" to HI 35¾"
Electric Articulation (Frame attachment choice)	15" or 11¾"	21", 17" or 13¼"	34" or 27¾" / <mark>50¾ or 44½"</mark>
Electric Hi-Lo Combo (LO to HI Settings based on frame attachment)	LO 11½" to HI 1¼" below rail	LO 21¼" to HI 11" or LO 16" to HI 5¾"	LO 30½" to HI 20¾" / LO 47½" to HI 37¼"
FOUNDATION MATTRESS TO FLOOR HEIGHTS The distance from the top of the mattress to the floor.			
Fixed w/Box Spring (Frame attachment choice)	23¾" or 27"	28", 32" or 35½"	23¾" or 30"
Fixed w/Bunkie Board (Frame attachment choice)	18½" or 21¾"	18¾" or 24"	18½" or 24¾"
Manual Articulation (Frame attachment choice)	20¾" or 24"	25", 28¾" or 32½"	20¾" or 27"
Manual Electric Combo (LO to HI Settings based on frame attachment)	LO 24¼" to HI 36"	LO 24½" to HI 36¼" or LO 29¾" to HI 41½"	LO 241/4" to HI 36"
Manual Hi-Lo (LO to HI Settings based on frame attachment)	LO 24¼" to HI 36"	LO 241/2" to HI 361/4" or LO 293/4" to HI 411/2"	LO 241/4" to HI 36"
Manual Hi-Lo Combo (LO to HI Settings based on frame attachment)	LO 24¼" to HI 36"	LO 241/2" to HI 361/4" or LO 293/4" to HI 411/2"	LO 241/4" to HI 36"
Electric Articulation (Frame attachment choice)	20¾" or 24"	25", 28¾ or 32½"	20¾" or 27"
Electric Hi-Lo Combo (LO to HI Settings based on frame attachment)	LO 24¼" to HI 34½"	LO 24½" to HI 34¾" or LO 29¾" to HI 40"	LO 241/4" to HI 341/2"
FLOOR TO RAIL HEIGHT The distance from the floor to the top of the rail.	35¾"	45¾"	54¾" / <mark>72"</mark>
OVERALL OUTSIDE DIMENSIONS	1		
Twin	42¼"W x 80½"L x 40¾"H	42¼"W x 80½"L x 50¾"H	42¼"W x 80¼"L x 57"H (72¾"H w/Ext.)
Full	56"W x 80"L x 40¾"H	56"W x 80"L x 50¾"H	56" W x 80" L x 57"H (72¾"H w/Ext.)
Queen	65"W x 80"L x 40¾"H	65"W x 80"L x 50¾"H	65"W x 80"L x 57"H (72¾"H w/Ext.)
MATTRESS SIZE Width without pads / Width with pads / Leng	rth		
Twin/Full/Queen	38"W / 36"W / 77"L	52"W / 50"W / 77"L	61"W / 60"W / 77"L
UNDER BED FLOOR CLEARANCE			
Standard Models	8"	8"	7¾"
TRANSFER HEIGHT The distance from top edge of the folded down safety rail to the floor.	221/4"	32"	26"











SleepSafe®

SleepSafer®